


### 电路原理图



### Technical characteristics

技术特征

Service condition: -30 ~70°

使用条件: -30 ~70°

Rated load: DC30V 0.5A

额定负载: DC30V 0.5A

Contact resistance: ≤0.03 Ω

接触电阻: ≤0.03 Ω

Insulation resistance: ≥100MΩ DC250V

绝缘电阻: ≥100MΩ DC250V

Pressure: AC500V(50HZ)/min


压力: AC 500v(50HZ)/分钟

Insertion and pulling force: 3~20N

插拔力: 3~20N



Life expectancy: 5000

寿命: 5000



零件序号

### PCB板位置尺寸 TOP VIEW



|            | MATERIAL        | PLATING |
|------------|-----------------|---------|
| terminal 1 | Phosphor Bronze | tin     |
| terminal 2 | Phosphor Bronze | tin     |
| terminal 3 | Phosphor Bronze | tin     |
| plastic    | PPA             |         |

广东星坤科技股份有限公司

|      |             |
|------|-------------|
| Δx   | 日期          |
| Δx   | 日期          |
| Δx   | 日期          |
| MARK | DESCRIPTION |

文件工程章

| REVISIONS | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------|------|---------|----------|------------------------|
|           |      |         |          |                        |

|             |      |
|-------------|------|
| ANGLAR      | ±5°  |
| L ≤ 4       | ±0.2 |
| 4 < L ≤ 16  | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63      | ±0.5 |



|      |             |
|------|-------------|
| DSND | SCALE: N/A  |
| DWN  | VIEW:       |
| CHKD | UNIT: mm/in |
| APPD | SIZE: A4    |

|             |                |         |
|-------------|----------------|---------|
| MODEL TYPE: | 3.5 PHONE JACK |         |
| PART NO.:   | PJ-326-SMT     |         |
| DWG NO.:    | X-PJ-326-SMT   |         |
| WEIGHT      | SHEET          | REVISIC |
|             | 1/1            | A0      |