







技术要求:

- 1、接触电阻: $<30\text{m}\Omega$
- 2、绝缘电阻: $>100\text{M}\Omega$
- 3、耐电压:AC 500V 1min无飞弧及击穿
- 4、寿命:5000 10~20次/min
- 5、额定负载:DC 30V/0.5A
- 6、适用温度范围:-20~70

序号	名称	材料	镀层/颜色	备注
1	1号弹片	磷铜	镀银	
2	2号弹片	磷铜	镀银	
3	3号弹片	磷铜	镀银	
4	基座	PBT	黑色	

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	PJ-313B-6P	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	PJ-313B-6P			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
							ANGULAR ±3°		
							FILE.NO.		