





Color : B:Black: W:White

H(mm) : 20:2.0,30: 3.0,40: 4.0

额定电压:DC12V 0.1A  
绝缘电阻: > 100MΩ  
对压强度: AG250V(50Hz)1min  
环境温度: -25℃ ~ +70℃  
相对湿度: (40 ~ 95%)<95%  
接触电阻: <50MΩ  
动作力: 200gf+20gf  
耐高温度: 260℃

|          |         |              |                |                        |                                          |            |          |            |      |
|----------|---------|--------------|----------------|------------------------|------------------------------------------|------------|----------|------------|------|
| _____    |         | new          |                | 2015/5/3               |                                          | A          |          | 瀚源         |      |
| ECN BO.  |         | DESCRIPTION. |                | DATE.                  |                                          | REV.       |          |            |      |
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER |                        |                                          | SCALT: 1/2 |          | SCALE: 3:1 |      |
| Mikey    | Tom     | Jerry        | PART NAME      | MST22D18G-X-X          | UNLESS OTHERWISE<br>SPECIFIED,TOLERANCE: |            | X.       | ±0.25      |      |
|          |         |              | MODEL NAME     | MST22D18G-X-X          |                                          |            | X.x      | ±0.20      |      |
|          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD |                                          |            |          |            | X.xx |
|          |         |              |                |                        |                                          |            | ANGULAR  | ±3°        |      |
|          |         |              |                |                        |                                          |            | FILE.NO. |            |      |