

Specifications:

规格:

1. Voltage rating: 250V AC/DC
额定电压: 250V AC/DC
2. Current rating: 3A AC/DC
额定电流: 3A AC/DC
3. Withstanding voltage: 500V AC/minute
耐受电压: ≥500V AC/分钟
4. Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C
5. Insulation resistance: 1000MΩMIN
绝缘电阻: ≥1000MΩ
6. Contact resistance: 30mΩMax
接触电阻: ≥30mΩ

Material:



材料:

7. Rubber core: PBT UL94V-0
胶芯: PBT UL94V-0
 8. The iron shell: SPCC Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC, 镀镍/镀锡/镀金
- B、成品不能有弯针，R角不一致等不良。

X05 XX F X X X X

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No. Pin No. XX-15; 26; 44; 62
- ③ Welding Board Angle : F-Female
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7: AuSn
- ⑥ Color: B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7



NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
15	16.35	24.99	30.80	19.28
26	24.75	33.32	39.20	27.51
44	38.35	47.04	53.50	41.28
62	54.75	63.50	69.40	57.71

铆合方式	TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝
图示				

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: D-USB
DWN	VIEW:	PART NO.: X05XXFXXXX
CHKD	UNIT: mm/in	DWG NO.: X-X05XXFXXXX
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED