




## NOTES

Used in DL20017-Y Series Housing.




Accepts AWG #22~28 Wire Range.

Material : Phosphor Bronze .

Finish: Tin plated.

Qty/Reel: 12,000 PCS.

Thickness: 0.2 mm.



| TYPE     | Dimension mm |     |     |     | 适用线规AWG |
|----------|--------------|-----|-----|-----|---------|
|          | A1           | B1  | A2  | B2  |         |
| PHDS-T-G | 2.0          | 2.3 | 1.5 | 1.5 | #26-22  |
| PHDS-T-D | 1.8          | 1.6 | 1.4 | 1.2 | #28-24  |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |               | ZHE JIANG DELI CONNECTORS CO., LTD |               |                                               |           |
|------------------------------------------|---------------|------------------------------------|---------------|-----------------------------------------------|-----------|
| .X: ± 0.25                               | X° : ± 3.0°   | PRODUCT NAME:                      |               | TITLE:                                        |           |
| .XX: ± 0.15                              | .X° : ± 2.0°  | DL20017 (PHDS) -T                  |               | 2.00 mm Pitch<br>Wire To Board Crimp Terminal |           |
| .XXX: ± 0.01                             | .XX° : ± 1.0° | DR: Yuan Junrong                   | DATE: 21.12.5 | PART NO:                                      |           |
| FINISH:                                  |               | CHKD: Wu Hui                       | DATE: 21.12.5 | SCALE: N/A                                    | PAGE: 1/1 |
| DRAWING NO:                              |               | APPD: Ren An De                    | DATE: 21.12.5 | UNITS: mm                                     | REV.: A   |