







P.C.B LAYOUT

Specifications:

规格:

Current rating:5A AC/DC

额定电流: 5A AC/DC

Voltage rating:250V AC

额定电压: 250V AC

Withstanding voltage:500V AC/MIN

耐受电压: ≥500V AC/分钟

Temperature range:-55℃~+105℃

温度范围: -55℃~+105℃

Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

Contact resistance:30mΩMAN

接触电阻:≤30mΩ

Material And FINISHED:

材料和成本:

INSULATOR:PBT UL 94V-0

绝缘体: PBT UL 94V-0

SHELL: SPCC-SD Plated Ni / Au / Sn

外壳: 铁合金 镀镍/金/锡

CONTACT MATERIAL:COPPER ALLOY

触点材料: 铜合金

X03 XX F C X X X

① ② ③ ④ ⑤ ⑥ ⑦

① Series N0.

② Row No.Pin No:XX-09;15;25;37


③ Welding Board Angle :F-Female

④ C: Car-pin

⑤ Planting Categoty:1:1U' ;2:2U' ;3:3U' ;4:5U' ;5:15U' 6:30U' ;7:AuSn

⑥ B:Black W:White BL:Blue Y:Yellow G:Green R:Red

⑦ 1:TYPE-1; 2:TYPE-2



NO.OF CONTACT	A±0.25	B±0.13	C±0.38	D
09	16.33	24.99	30.81	11.08
15	24.66	33.32	39.14	19.39
25	38.38	47.04	53.04	33.24
37	54.84	63.50	69.32	49.86

							DSND		SCALE: N/A	MODEL TYPE: D-USB			
ΔX					ANGLAR	±5°		DWN		VIEW: 	PART NO.: X03XXFCXXX		
ΔX					L ≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.: X-X03XXFCXXX		
ΔX					4<L ≤ 16	±0.3		APPD		SIZE: A4			
ΔX					16<L ≤ 63	±0.4							
MARK		DESCRIPTION	DATE	REVISED	APPROVED	L > 63							
REVISIONS							UNSPECIFIED TOLERANCES				WEIGHT		
www.helloxb.com www.helloxb.cn www.xk-dg.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED				SHEET		
											1/1		
											REVISION		
											A0		