




A4			
A3			
A2			
A1			
REV	DATE	REVISION DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91650P124RA

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

A		B		C		D		E		F		G	
1	性能参数												1
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. Compression torque: ≤ 3.5N 按压扭力: ≤3.5N						
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min						15. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. mechanical: 500000cycles 机械寿命: 500000cycles						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. Operation method:Self-locking type 操作方式: 自锁式						
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10						18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10						19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃						20. LED lamp lifespan: 40000h LED寿命: 40000h						
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						21. LED color: Red LED颜色: 红色						
2													2
3													3
4	连接形式												4
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)												
	2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极												
5													5
A4													
A3													
A2													
A1													
REV DATE REVISION DESCRIPTION ISSUE													
A B C D E F G													

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91650P124RA		
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR							Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission
A		B		C		D		E		F		G	

A					B					C					D					E					F					G				
1																																		
材质参数																																		
10					luminous zone 发光区					PC 塑料					1																			
9					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银														
8					Base 底座					PA46					1																			
2																																		
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银														
5					LED Base LED基座					PBT					1																			
3																																		
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														
4																																		
5																																		
A4										 ROCPCU					COMMON TOLERANCE					UNIT		MM		PROJECTED				PRODUCT NAME:						
A3															DRAWN BY		FUYUAN		CHECKED BY		COCO		MODEL NO: TP91650P124RA											
A2															DATE		2019		APPROVAL B		ALEN		Https: www.rocpcu.tw											
A1															ROCPCU TECHNOLOGY CO.,LTD																			
REV					DATE		REVISION								DESCRIPTION		ISSUE		ANGULAR				Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission											
A					B					C					D					E					F					G				