





Main technical specifications:

主要技术规格:

- Rated value: 50mA DC12V
- 额定值: 50mA DC12V
- Contact resistance: $\leq 50m\Omega$
- 接触电阻: $\leq 50m\Omega$
- Operating force: $260 \pm 30gf$
- 操作力: $260 \pm 30gf$
- Stroke: $0.30 \pm 0.1mm$
- 行程: $0.30 \pm 0.1mm$
- Insulation resistance: $\geq 100m\Omega$
- 绝缘电阻: $\geq 100M\Omega$
- Electric strength: 250V 50Hz 1min
- 抗电强度: 250V 50HZ 1Min.
- Service life: 100000 cycles
- 寿命: 100,000 Cycles
- Waterproof grade: IP67
- 防水等级: IP67
- Anti silver migration: 60V, 85 °C, 90% RH / 60H
- 防银迁移: 60V, 85°C, 90%RH/60H
- Working temperature: - 40 °C to + 85 °C
- 工作温度: -40°C to + 85°C



Circuit diagram



PCB welding diagram

6	Terminal 端子	Brass 黄铜	1	Ag plating 镀银
5	Base 底座	PPA	1	Black 黑色
4	Contact 弹片	SUS	1	Ag plating 镀银
3	Waterproof pad 防水垫	Silica gel 硅胶	1	Black 黑色
2	Cover 盖板	SUS	1	
1	Stem 按钮	PPA	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TPF16LS-SC45	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
						X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
A		B		C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission