





P.C.B LAYOUT
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

A4				COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: SK-22D02-3
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				
REV	DATE	REVISION	DESCRIPTION	ISSUE					