










面板最大厚度5.50 [0.217]



Schematic Diagram
电气原理图



Installation View
安装视图



A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91641P124RA
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A						13. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
	2. Rated current:2A/DC36V 额定电流:2A/DC36V						14. mechanical: 500000cycles 机械寿命: 500000cycles						
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min						15. Operation method:Self-locking type 操作方式: 自锁式						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10						18. LED lamp lifespan: 40000h LED寿命: 40000h						
	7. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10						19. LED color: Red LED颜色: 红色						
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	9. Protection level:IP67 防护等级:IP67												
2	10. Explosion prevention level: IK09 防暴等级: IK09												
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	12. Compression torque: ≤ 3N 按压扭力: ≤3N												
3													
4													
5													
A4													
A3													
A2													
A1													
REV		DATE		REVISION DESCRIPTION		ISSUE							
A		B		C		D		E		F		G	



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	——

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91641P124RA
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
ROC PU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G																																																										
1	材质参数 <table border="1"> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>8</td><td>LEDpin LED脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>Silvering 镀银</td><td>1</td><td></td></tr> <tr> <td>5</td><td>Base 基座</td><td>PA66</td><td>1</td><td>Black 黑色</td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>Aluminum alloy 铝合金</td><td>1</td><td>Oxidized/Black 氧化/黑色</td></tr> <tr> <td>1</td><td>Key 按键</td><td>Aluminum alloy 铝合金</td><td>1</td><td>Oxidized/Black 氧化/黑色</td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>																	8	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银	7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	Contact material 接触材质	Silvering 镀银	1		5	Base 基座	PA66	1	Black 黑色	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1		
8	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银																																																													
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																													
6	Contact material 接触材质	Silvering 镀银	1																																																														
5	Base 基座	PA66	1	Black 黑色																																																													
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																													
3	Oring O型圈	Silica gel 硅胶	1																																																														
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色																																																													
1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色																																																													
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																													
2								2																																																									
3								3																																																									
4								4																																																									
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td> <td colspan="2">COMMON TOLERANCE</td> <td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td> <td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP91641P124RA</td></tr> <tr> <td>A2</td><td></td><td></td><td></td> <td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td> <td colspan="7"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td> <td colspan="2">ANGULAR</td><td colspan="5">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91641P124RA			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																						
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91641P124RA																																																								
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																								
A1					ROCPCU TECHNOLOGY CO.,LTD																																																												
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																									
	A	B	C	D	E	F	G																																																										