




A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91643P124RA
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO., LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A						13. mechanical: 500000cycles 机械寿命: 500000cycles						
	2. Rated current:2A/DC36V 额定电流:2A/DC36V						14. Operation method:Self-locking type 操作方式: 自锁式						
	3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	5. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10						17. LED lamp lifespan: 40000h LED寿命: 40000h						
	6. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10						18. LED color: Red LED颜色: 红色						
	2	7. Nut assembly torque:5-14N 螺帽装配力矩:5-14N											
8. Protection level:IP67 防护等级:IP67													
9. Explosion prevention level: IK09 防暴等级: IK09													
10. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃													
11. Compression torque: ≤ 3N 按压扭力: ≤3N													
12. Electrical life: 500000 cycles 电气寿命: 500000 cycles													
3													
	4												
5													

A	B	C	D	E	F	G		
1 1 材质参数								
9	luminous zone 发光区	PC 塑料	1					
8	LEDpin LED脚	Brass 黄铜	1		Silvering 镀银			
7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金			
6	Contact material 接触材质	silver alloy 银合金	1		Silvering 镀银			
5	Base 基座	PA66	1		Black 黑色			
4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍			
3	Oring O型圈	Silica gel 硅胶	1					
2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色			
1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色			
NO 序号	Part name 部件名	Material 材料	QTY 数量		Remark 备注			
4 4								
A4				UNIT	MM	PROJECTED		
A3				DRAWN BY	FUYUAN	CHECKED BY		
A2				DATE	2019	APPROVAL B		
A1								
REV	DATE	REVISION	DESCRIPTION	ISSUE				
5 5  台普 ROCPCU				COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR			PRODUCT NAME: MODEL NO: TP91643P124RA Https: www.rocpcu.tw	
				ROCPU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission								
A	B	C	D	E	F	G		