




A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:						
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91642G224RA						
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw						
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD										
					X	± 0.25											
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	_____		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission.								
				A		B		C		D		E		F		G	

	A		B		C		D		E		F		G	
1	性能参数 1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A 2. Rated current:2A/DC36V 额定电流:2A/DC36V 3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 5. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10 6. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10 7. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 8. Protection level:IP67 防护等级:IP67 9. Explosion prevention level: IK09 防暴等级: IK09 10. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 11. Compression torque: ≤ 3N 按压扭力: ≤3N 12. Electrical life: 500000 cycles 电气寿命: 500000 cycles 13. mechanical: 500000cycles 机械寿命: 500000cycles 14. Operation method:Self repeating form 操作方式: 自复式 15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 17. LED lamp lifespan: 40000h LED寿命: 40000h 18. LED color: Red LED颜色: 红色													1
2														2
3														3
4														4
5	A4				台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3				DRAWN BY				FUYUAN	CHECKED BY	COCO	MODEL NO: TP91642G224RA			
A2				DATE				2019	APPROVAL B	ALEN	Https: www.rocpu.tw			
A1				X.XX				± 0.10	ROC PU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION	ISSUE				X.X					± 0.15	
						X	± 0.25	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						
						ANGULAR	—							
	A		B		C		D		E		F		G	

A					B					C					D					E					F					G				
材质参数																																		
9					luminous zone 发光区					PC 塑料					1																			
8					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银														
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					Silvering 镀银					1																			
5					Base 基座					PA66					1					Black 黑色														
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														

A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91642G224RA
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					