

# USB 3.2 Gen 1 Active Extension Cable - USB-C to USB-A (M/F), 5 Gbps, Data Only, 5 m (16.4 ft.)

MODEL NUMBER: U330-05M-C2A



Active 16 ft. extension cord increases the distance between 2 connected USB devices, including Chromebooks, without signal loss.

## Features

**5 m Extension Cable Connects Computers, Printers, Modems and Other USB Equipment** This USB-C to USB-A Active Extension Cable (M/F) attaches to your current USB 3.0 cable to extend it by 16.4 feet (5 meters). It connects your computer, tablet, notebook, MacBook, Chromebook, smartphone or other compatible USB-C device to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. The 16.4-foot length allows you great flexibility in placing equipment.

**Built-In Signal Booster for Peak Performance** Just connect the active cable's USB-C plug to your computer's USB port and the USB-A female connector to a USB device cable to extend your total connection beyond USB's natural 16.4-foot limit. The bus-powered signal booster ensures USB 3.1 Gen 1 data transfer speeds up to 5 Gbps with no signal loss. The cable is backward compatible with previous USB generations, so you can use it with legacy equipment.

**770mA of Proper Power to Keep Devices Functioning** The U330-05M-C2A works with standard USB 3.0 cables and provides up to 770mA of power to a connected device. For power applications stronger than 770mA, you must connect a compatible DC 5V external power supply with a barrel connector of 3.5 x 1.35 x 7.5 mm; positive pin, negative sleeve (sold separately).

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C port in either direction for a fumble-free connection every time.

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332243904 |
| Technology | USB 3.x      |
| Cable Type | Active       |

## Highlights

- Adds 5 m (16.4 ft.) to your existing USB connection to provide flexibility in placing devices
- Provides up to 770mA of power to connected device without need for external power
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps -- 10x faster than USB 2.0
- Connects your existing USB-A devices to newer laptops or tablets featuring USB-C ports

## Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 16.4 ft. to more easily place a device
- Provide a high-quality replacement for a worn-out or missing extension cable

## System Requirements

- USB 3.0 computer port and USB 3.0 connected device required to meet USB 3.0 speeds
- External power supply required if connected device needs more than 770mA of power

## Package Includes

- U330-05M-C2A USB-C Active Extension Cable, USB-C to USB-A (M/F), 16.4 ft. (5 m)



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

| INPUT                                 |   |
|---------------------------------------|---|
| Voltage Compatibility (VDC)           | 5V  |
| Bus Powered                           | Yes   |
| POWER                                 |   |
| DC Barrel Plug                        | OD: 3.5 x 1.35 x 7.5mm, Positive Pin, Negative Sleeve |
| CONNECTIONS                           |   |
| Side A - Connector 1                  | USB C (MALE)  |
| Side B - Connector 1                  | USB 3.0 A (FEMALE)                                    |
| Connector Plating                     | Nickel  |
| Connector Style                       | Straight  |
| USER INTERFACE, ALERTS & CONTROLS     |   |
| LED Indicators                        | (x1) Blue LED (Power)                                 |
| PHYSICAL                              |   |
| Material of Construction              | Aluminum, PVC   |
| Cable Jacket Color                    | Black   |
| Cable Jacket Rating                   | VW-1  |
| Cable Length (ft.)                    | 16.4  |
| Cable Length (m)                      | 5.00  |
| Shipping Dimensions (hwd / in.)       | 10.00 x 7.00 x 0.50                                   |
| Shipping Weight (lbs.)                | 0.51  |
| Unit Packaging Type                   | Polybag   |
| Unit Weight (lbs.)                    | 0.51  |
| Unit Weight (kg)                      | 0.23  |
| ENVIRONMENTAL                         |   |
| Operating Temperature Range           | 32° to 104°F (0° to 40°C)                             |
| Storage Temperature Range             | -4° to 140°F (-20° to 60°C)                           |
| Relative Humidity                     | 0% to 90% RH, Non-Condensing                          |
| Power Provided to Connected Device(s) | Up to 0.77A   |
| FEATURES & SPECIFICATIONS             |   |
| USB Specification                     | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)  |
| Driver Required                       | No  |

| STANDARDS & COMPLIANCE              |                                     |
|-------------------------------------|-------------------------------------|
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT                  |                                     |
| Product Warranty Period (Worldwide) | 3-year limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.