






REV	ECN NO.	APPD
A	HG-19-0067	PROJOM

规格 Specifications	
额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC 100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±30gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.2±0.1mm



RECOMMENDED P.C.B. LAYOUT
安装尺寸图



PRODUCT NO.: 1TS002T****-***** A9 - CT

- 轻触开关
- 3X6系列
- 外形:
- A=插脚
 - B=贴片
 - C=贴片带柱8.8
 - L=贴片10.2
 - J=侧按无柱
 - T=侧按支架带柱
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 操作力度:
- 100=100gf
 - 120=120gf
 - 160=160gf
 - 250=250gf
 - 300=300gf
- 初始颜色
- 则不启用
- 材质:
- 0=初始材质
 - 1=新增材质
 - 依次增加
- 产品高度(H):
- 330=3.3mm
 - 350=3.5mm
 - 380=3.8mm
 - 430=4.3mm
- 手感:
- 0=常规
 - 1=大手感
 - 2=小手感
 - 3=特殊手感
- 编织带
- 非编织带, 不启用

5	COVER	1	BRASS	Ag-PLATED
4	ACTUATOR	1	LCP/硅胶	WHITE/BLACK/BLUE
3	DOME	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	LCP/PPA	WHITE/BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
X. ± 0.3	X' ± 3'	UNITS	NAME(INTENDED USE)	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
X ± 0.2	X' ± 2'	MAT'L	3X6 SMT SERIES TACT SWITCH	
.XX ± 0.1	.XX' ± 1'	FINISH	PART NO.(INTENDED USE)	
.XXX ± 0.05	.XXX' ± 0.5'		ITS002T-1600-3500A9-CT	
			APPD: W.P.LU 2019.4.23	
	Q'TY		CHKD: S.L.Li 2019.4.23	PRODUCT DRAWING
		DR:	Y.Y.Chen 2019.4.23	DWG NO.: ITS002T-1600-3500A9-CT
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.				
				SCALE SHEET REV.
				10/1 1/1 A