







RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	260±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm

PRODUCT NO.: 1TS 005F****0****0A2 - CT

轻触开关 系列: 外形: 按钮颜色: 底座颜色: 盖板颜色: 操作力度: 120=120gf 160=160gf 200=200gf 260=260gf 0=常规(弹片) 材质: 0=初始材质 1=新增材质 依次增加 产品高度(H): 430=4.3mm 500=5.0mm 600=6.0mm 700=7.0mm 800=8.0mm 900=9.0mm 编带 非编带, 不启用

产品高度(H):

按钮颜色:
底座颜色:
盖板颜色:
操作力度:
120=120gf
160=160gf
200=200gf
260=260gf
0=常规(弹片)

初始颜色, 则不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	BRASS	Ni-PLATED
4	ACTUATOR	1	PPA	BLACK
3	DOME	1	Stainless Steel/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK

UNITS	MM	NAME(INTENDED USE)	HON YUAN
X. ± 0.3	X' ± 3'	6X6 SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
X. ± 0.2	X' ± 2'	PART NO.(INTENDED USE)	TITLE:
.XX ± 0.1	.XX' ± 1'	1TS005F-2600-8000A2	PRODUCT DRAWING
.XXX ± 0.05	.XXX' ± 0.5'	APPD: W.P.Lu 2018.3.31	DWG NO.: 1TS005F-2600-8000A2-CT
		CHKD: S.L.Li 2018.3.31	
		DR: Y.Y.Chen 2018.3.31	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN

SCALE	SHEET	REV.
10/1	1/2	A