





REV	ECN NO.	APPD
B	HL-19-0189	ZO

规格 Specifications

额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	500mΩ max.	
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	炉前200±50gf	炉后220±50gf
寿命试验 Operating Life	50,000 cycles	
行程 Travels	0.13±0.08mm	



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

LAND PATTERN PLAN
印刷电路板焊盘参考图

PRODUCT NO. : 1TS015A***-*****A30 - **

- 轻触开关
- 3X2系列
- 外形:
- A=两脚
- B=两脚无按柄
- 触点颜色:
- 底座颜色:
- 贴膜颜色:
- 操作力度:
- 手感:
- 材质:
- 其它:
- CT=编带 (非编带, 不启用)
- 产品高度 (H):
- 初始颜色
- 则不启用
- 0=常规 (弹片)
- 1=大手感 (弹片)
- 2=小手感 (弹片)
- 3=特殊手感 (弹片)
- 0=初始材质
- 1=新增材质
- 3=3个弹片
- 依次增加
- 060=0, 60mm
- 065=0, 65mm
- 070=0, 70mm
- 100=100gf
- 120=120gf
- 160=160gf
- 180=180gf
- 200=200gf
- 220=220gf
- 240=240gf
- 330=330gf

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	KNOB	1	POLYAMIDE	BLACK
4	FILM	1	POLYAMIDE	WHITE
3	DOME	2	SUS301	Ag-PLATED
2	HOUSING	1	POLYAMIDE	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED
NAME (INTENDED USE)	NAME (INTENDED USE)	NAME (INTENDED USE)	NAME (INTENDED USE)	NAME (INTENDED USE)
3X2 SERIES TACT SWITCHES	3X2 SERIES TACT SWITCHES	3X2 SERIES TACT SWITCHES	3X2 SERIES TACT SWITCHES	3X2 SERIES TACT SWITCHES
PART NO. (INTENDED USE)	PART NO. (INTENDED USE)	PART NO. (INTENDED USE)	PART NO. (INTENDED USE)	PART NO. (INTENDED USE)
1TS015A-2000-0600A30	1TS015A-2000-0600A30	1TS015A-2000-0600A30	1TS015A-2000-0600A30	1TS015A-2000-0600A30
APPD: ZO 7/22/2019	APPD: ZO 7/22/2019	APPD: ZO 7/22/2019	APPD: ZO 7/22/2019	APPD: ZO 7/22/2019
CHKD: M.H.Li 7/22/2019	CHKD: M.H.Li 7/22/2019	CHKD: M.H.Li 7/22/2019	CHKD: M.H.Li 7/22/2019	CHKD: M.H.Li 7/22/2019
DR: Y.Y.Chen 7/22/2019	DR: Y.Y.Chen 7/22/2019	DR: Y.Y.Chen 7/22/2019	DR: Y.Y.Chen 7/22/2019	DR: Y.Y.Chen 7/22/2019
DWG NO.: 1TS015A-2000-0600A30-CT	DWG NO.: 1TS015A-2000-0600A30-CT	DWG NO.: 1TS015A-2000-0600A30-CT	DWG NO.: 1TS015A-2000-0600A30-CT	DWG NO.: 1TS015A-2000-0600A30-CT
SCALE	SHEET	REV.	SCALE	SHEET
25/1	1/1	B	25/1	1/1