






REV	ECN NO.	APPD
A	HG-17-0093	PROJOM

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.18±0.05mm



PRODUCT NO. : 1TS004ABB -***** A1 - CT

轻触开关
3X3系列
外形:
材料:
0=初始材质
1=新增材质
依次增加
产品高度(H):
150=1.50mm
200=2.00mm
手感:
0=常规(45~75%)
1=大手感
2=小手感
3=特殊手感
编织带
非编织带,不启用

操作力度:
160=160gf
250=250gf

5	盖板	1	不锈钢	/
6	按钮	1	LCP	灰色
4	防尘膜	1	PI	黄色
3	弹片	2	不锈钢覆银	镀银
2	底座	1	LCP	灰色
1	卡件	1	GS191	镀银
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
NAME(INTENDED USE)				
3X3 SERIES				
TACT SWITCH				
PART NO.(INTENDED USE)				
1TS004ABB-1600-2000A1				
TITLE: PRODUCT DRAWING				
DWG NO.: 1TS004ABB-1600-2000A1-CT				
CHKD: S.Li 2017.12.07				
DR: Y.Y.Chen 2017.12.07				
SCALE SHEET REV. 15/1 1/1 A				