







规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	260±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

5	COVER	1	BRASS	Ni-PLATED
4	ACTUATOR	1	PPA	BLACK
3	DOME	1	Stainless Steel/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'	UNITS	NAME(INTENDED USE)	HON YUAN
X ± 0.2	X' ± 2'	MAT'L	6X6 SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD.
.XX ± 0.1	.XX' ± 1'	FINISH	PART NO.(INTENDED USE)	SHENZHEN, CHINA.
.XXX ± 0.05	.XXX' ± 0.5'		1TS005F-2600-6000A2	PRODUCT DRAWING

APPD:	W.P.Lu 2018.3.31	DWG NO.:	1TS005F-2600-6000A2-CT
CHKD:	S.L.Li 2018.3.31		
DR:	Y.Y.Chen 2018.3.31		

SCALE SHEET REV.

REV.

A

PRODUCT NO.: 1TS 005F****0****0A2 - CT

轻触开关

系列:

外形:

按钮颜色:

底座颜色:

盖板颜色:

初始颜色, 则不启用

操作力:

手感:

材质:

产品高度(H):

材质:

0=初始材质

1=新增材质

依次增加

430=4.3mm

500=5.0mm

600=6.0mm

700=7.0mm

800=8.0mm

900=9.0mm

①

②

③

④

非编带

编带

非编带, 不启用

非编带, 不启用

非编带, 不启用

非编带, 不启用

非编带, 不启用

非编带, 不启用