



CIRCUIT DIAGRAM



回路图



RECOMMENDED P.C.B. LAYOUT

安装尺寸图

规格 Specifications	
额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	260±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm



PRODUCT NO.: 1TS002B***-*****A2 - CT

- 轻触开关
- 3X6系列
- 外形:
- A=插脚
- B=贴片
- C=贴片带柱
- E=贴片2.5高
- K=贴片带柱8.8
- L=贴片10.2
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 操作力度:
- 手感:
- 产品高度 (H):
- 材质:
- 0=Pb66
- 1=LCP+PPA
- 2=LCP
- 3=LCP+PPA(双弹片)
- 4=新增材质
- 依次增加
- 非编带
- 编带
- 0=常规
- 1=大手感
- 2=小手感
- 3=特殊手感
- 初始颜色
- 则不启用
- 130=130gf
- 160=160gf
- 180=180gf
- 220=220gf
- 250=250gf
- 260=260gf
- 300=300gf

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	LCP	WHITE
4	COVER	1	STAINLESS STEEL	NATURAL
3	DOVE	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	PPA	WHITE
1	TERMINAL	1	BRASS	Ag-PLATED
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
X. ± 0.3	X' ± 3'	UNITS	MM	
X ± 0.2	X' ± 2'	MATL		
.XX ± 0.1	.XX' ± 1'			
.XXX ± 0.05	.XXX' ± 0.5'	FINISH		
NAME(INTENDED USE)	3X6 SMT SERIES	TACT SWITCH		
PART NO.(INTENDED USE)	1TS002B-2600-5001A2			
APPD:	ZO 2012/2/12			
CHKD:	M.H.Li 2012/2/12			
DR:	WP.LU 2012/2/12			
DWG NO.:	1TS002B-2600-5001A2-CT			
TITLE:	PRODUCT DRAWING			
HON YUAN	HON YUAN PRECISION IND. CO.,LTD.			
	SHENZHEN, CHINA, R.O.C.			
SCALE	SHEET	REV.		
10/1	1/1	A		

REV	ECN NO.	APPD
A	HS-12-0027	PRUJOM