






REV	ECN NO.	APPD
B	HG-19-0189	ZO

规格 Specifications

额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	500mΩ max.	
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	炉前 160±50gf	炉后 180±50gf
寿命试验 Operating Life	50,000 cycles	
行程 Travels	0.13±0.08mm	



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

LAND PATTERN PLAN
印刷电路板焊盘参考图

PRODUCT NO. : 1TS015A***-*****A30 - **

- 轻触开关
- 3X2系列
- 外形:
- A=两脚
- B=两脚无按柄
- 触点颜色:
- 底座颜色:
- 贴膜颜色:
- 操作力度:
- 手感:
- 材质:
- 其它:
- CT=编带 (非编带, 不启用)
- 产品高度 (H):
- 初始颜色
- 则不启用
- 0=常规 (弹片)
- 1=大手感 (弹片)
- 2=小手感 (弹片)
- 3=特殊手感 (弹片)
- 0=初始材质
- 1=新增材质
- 3=3个弹片
- 依次增加
- 060=0, 60mm
- 065=0, 65mm
- 070=0, 70mm
- 100=100gf
- 120=120gf
- 160=160gf
- 180=180gf
- 200=200gf
- 220=220gf
- 240=240gf
- 330=330gf

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	KNOB	1	POLYAMIDE	BLACK
4	FILM	1	POLYAMIDE	WHITE
3	DOME	2	SUS301	Ag-PLATED
2	HOUSING	1	POLYAMIDE	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED
NAME (INTENDED USE)	HON YUAN			
3X2 SERIES TACT SWITCHES	HON YUAN PRECISION IND. CO., LTD.			
PART NO. (INTENDED USE)	SHENZHEN, CHINA, R.O.C.			
TITLE:	PRODUCT DRAWING			
APPD:	1TS015A-1600-0600A30			
CHKD:	M.H.L: 7/22/2019			
DR: Y.Y.Chen 7/22/2019	DWG NO.: 1TS015A-1600-0600A30-CT			
SCALE	SHEET	REV.		
25/1	1/1	B		