







规格 Specifications		
额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	100mΩ max.	
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	160±40gf	
寿命试验 Operating Life	100,000 cycles	
行程 Travels	0.25±0.1mm	

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

PRODUCT NO.: 1TS 005F****0****0A2 - CT

轻触开关
系列:
外形:
按钮颜色:
底座颜色:
盖板颜色:
操作力度:
120=120gf
160=160gf
200=200gf
260=260gf
手感:
0=常规(弹片)
材质:
0=初始材质
1=新增材质
依次增加
产品高度(H):
430=4.3mm
500=5.0mm
600=6.0mm
700=7.0mm
800=8.0mm
900=9.0mm
非编带
编带, 不启用

5	COVER	1	BRASS	Ni-PLATED
4	ACTUATOR	1	PPA	BLACK
3	DOME	1	Stainless Steel/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'	UNITS	NAME(INTENDED USE)	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
X ± 0.2	X' ± 2'	MAT'L	6X6 SERIES TACT SWITCH	
.XX ± 0.1	.XX' ± 1'	FINISH	PART NO.(INTENDED USE)	TITLE: PRODUCT DRAWING
.XXX ± 0.05	.XXX' ± 0.5'		1TS005F-1600-7000A2	DWG NO.: 1TS005F-1600-7000A2-CT
		APPD:	W.P.Lu 2018.3.31	SCALE SHEET REV.
		CHKD:	S.L.Li 2018.3.31	10/1 1/2 A
		DR:	Y.Y.Chen 2018.3.31	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN