








| 修订 | 标记 | 修改摘要 | 签名 | 日期 |
|-----------|----|---------|----|------------|
| REV NO | | NEW DWG | | 2016-03-12 |



SPECIFICATION:
 1.MATERIAL:
 HOUSING:LCP 30% G/F UL 94V-0 or PA46 UL 94V-0
 COLOR:BLACK
 CONTACT:C5191-H,T=0.25mm
 2.FINISH:
 CONTACT:1u"or15u"
 / GOLD/TIN PLATING ON CONTACT AREA
 100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
 50u" MIN.NICKEL UNDERPLATING OVER ALL
 3.ELECTRICAL
 3.1 CURRENT RATING: 1.5A PER PIN MIN.
 3.2 CONTACT RESISTANCE: 30m OHM MAX.
 3.3 INSULATION RESISTANCE: 500M OHM MIN.
 3.4 DIELECTRIC WITHSTANDING VOLTAGE: 500VAC.



| | | | | | | | | |
|---|-------|---|-----|---|-------------------------------------|-------|------|-------------|
|  | | 深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187 | | | | | | |
| -TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表 | |   | | TITLE: SATA 7+15P母座板下型带 产品名称: 螺母H=12.0 | | | | |
| X.X | ±0.30 | X.X° | ±3° | APPD: 核准: | PART NO: 产品编号: HDGCYLSY-SATA-108 | | | |
| X.XX | ±0.20 | X.XX° | ±2° | CHECK: 校对: 王建业 | DATE | SCALE | UNIT | CODE NUMBER |
| X.XXX | ±0.10 | X.XXX° | ±1° | DRAW: 绘图: 黄艳兰 | 2016-03-12 | 1:1 | mm | A001 |

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作