



## Specification:

1. Electrical Characteristics:  
Contact Current Rating: 3 Amperes Max.  
Rated Voltage: 30V Max.  
Dielectric Withstanding Voltage: AC 100V r.m.s.  
Insulation Resistance: 100 MΩ Minimum.  
Contact Resistance: 40 mΩ Maximum.
2. Environmental:  
Operating Temperature: -40°C~+85°C.
3. Mechanical Characteristics:  
Insertion Force: 5~20Nf.  
Withdrawal Force: 6~20Nf.  
Durability Cycles: 5000 Cycles.
4.  Make is FAI test Dimension  
▼ Make is major test Dimension

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

深圳市华德共创科技有限公司  
Shenzhen Huade co-create Technology Co., LTD  
电话: 0755-27111216 传真: 0755-29940187



-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		APPD* 核准:	TITLE: TYPE C 6P四脚插板无弹不 产品名称: 锈钢L=6.8			
X. X	±0.30	X. X° ±3°	CHECK: 校对:	王建业	DATE	SCALE
X. XX	±0.20	X. XX° ±2°	DRAW: 绘图:	黄艳兰	2016-03-12	UNIT
X. XXX	±0.10	X. XXX° ±1°	CODE NUMBER	A001	mm	