










规格 Specifications

额定负荷 Rating	DC 5V/5mA(DC 16V/50mAmax)
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.2±0.1mm



CIRCUIT DIAGRAM
回路图



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

PRODUCT NO.: 1TS008F*****BH - **

轻触开关

3X4系列

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

160=160gf

250=250gf

初始颜色
则不启用

手感:

0=常规(45-75%)

1=大手感

2=小手感

3=特殊手感

材质:

0=初始材质

1=新增材质

依次增加

产品高度(H):

250=2.5mm

其它:

CT=编带(非编带,不启用)

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	C5191	Sn-PLATED
4	ACTUATOR	1	LCP	WHITE
3	CONTACT	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	4	C5191	Ag-PLATED
1	HOUSING	1	LCP	WHITE

X. ± 0.3	X' ± 3	UNITS
X ± 0.2	X' ± 2	MATL
.XX ± 0.1	.XX' ± 1	
.XXX ± 0.05	.XXX' ± 0.5	FINISH

NAME(INTENDED USE)	3X4 SERIES
TACT SWITCH	
PART NO.(INTENDED USE)	1TS008F-1600-2500BH-CT

NAME	HON YUAN
SHENZHEN, CHINA, R.O.C.	

PRODUCT DRAWING	
-----------------	--

APPD:	W.P.LU 2018.04.08
CHKD:	S.L.Li 2018.04.08
DR:	K.Ding 2018.04.08

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.



SCALE SHEET REV.

15/1 1/1 A