



CIRCUIT DIAGRAM

回路图




规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	180±30gf
寿命试验 Operating Life	150,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



PRODUCT NO.: 1TS002B****-*****A2 - CT

- 轻触开关
- 3X6系列
- 外形:
- A=插脚
- B=贴片
- C=贴片带柱
- E=贴片2.5高
- K=贴片带柱8.8
- L=贴片10.2
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 操作力度:
- 手感:
- 0=常规
- 1=大手感
- 2=小手感
- 3=特殊手感
- 材质:
- 0=PA66
- 1=LCPP+PPA
- 2=LCPP
- 3=LCPP+PPA(双弹片)
- 4=新增材质
- 依次增加
- 产品高度(H):
- 430=4.3mm
- 500=5.0mm
- 带带
- 非带带, 不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	LCP	WHITE
4	COVER	1	STAINLESS STEEL	NATURAL
3	DOVE	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	PPA	WHITE
1	TERMINAL	1	BRASS	Ag-PLATED

X. ±	0.3	X' ±	3'	UNITS	MM
X. ±	0.2	X' ±	2'	MATL	
.XX ±	0.1	.XX' ±	1'		
.XXX ±	0.05	.XXX' ±	0.5'	FINISH	

NAME(INTENDED USE)	3X6 SMT SERIES	TACT SWITCH
PART NO.(INTENDED USE)	1TS002B-1800-4301A2	
APPD:	ZO 2012/2/12	
CHKD:	M.H.Li 2012/2/12	
DR:	WP.Lu 2012/2/12	

DWG NO.:	1TS002B-1800-4301A2-CT
TITLE:	PRODUCT DRAWING

SCALE	SHEET	REV.
10/1	1/1	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.

HON YUAN
HON YUAN PRECISION IND. CO., LTD.
SHENZHEN, CHINA, R.O.C.