








规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

PRODUCT NO.: 1TS 005F****0****0A2 - CT

轻触开关

系列

外形

按钮颜色

底座颜色

盖板颜色

初始颜色, 则不启用

操作力

手感

材质

产品高度(H)

非编带, 不启用

材质:
0=初始材质
1=新增材质
依次增加

产品高度(H):
430=4.3mm
500=5.0mm
600=6.0mm
700=7.0mm
800=8.0mm
900=9.0mm

操作力:
120=120gf
160=160gf
200=200gf
260=260gf

手感:
0=常规(薄片)

材质:
0=初始材质
1=新增材质
依次增加

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	BRASS	Ni-PLATED
4	ACTUATOR	1	PPA	BLACK
3	DOME	1	Stainless Steel/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK

UNITS	MM
X. ± 0.3	X' ± 3'
X. ± 0.2	X' ± 2'
.XX ± 0.1	.XX' ± 1'
.XXX ± 0.05	.XXX' ± 0.5'

NAME(INTENDED USE)	6X6 SERIES TACT SWITCH
PART NO.(INTENDED USE)	1TS005F-1600-6000A2
APPD:	W.P.Lu 2018.3.31
CHKD:	S.L.Li 2018.3.31
DR:	Y.Y.Chen 2018.3.31

DWG NO.:	1TS005F-1600-6000A2-CT
TITLE:	PRODUCT DRAWING
SCALE	SHEET
10/1	1/2
REV.	A

REV	ECN NO.	APPD
A	HG-18-0037	PROJOM