




2x03Pin 小鼻、单槽
Type B







2x04Pin 小鼻、单槽
Type B






一般型端子



2x05~2x06Pin
大鼻、单槽



2x07~2x32Pin 双槽



接触电阻: 20mΩ Max

<u>X9555</u>	<u>H3 - 2xXX</u>	<u>X - PT</u>	<u>V01</u>
(1)	(2)	(3)	(4) (5) (6)

- 1.Series No
- 2.Category:H3-Two piece with bow button
- 3.Row No.Pin No:2xXX-2x03~2x32P
- 4.Special No:Type A or Type B
Blank-Except for special Pin bits
- 5.Material:PT-PBT UL 94V-0
- 6.Plating:V01-Gold Flash over Nickel

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2x03	12.32	5.08	1.90	8.02	2x13	37.72	30.48	3.80	33.42
2x04	14.86	7.62	1.9/3.8	10.56	2x15	42.80	35.56		38.50
2x05	17.40	10.16	3.80	13.10	2x17	47.88	40.64		43.58
2x06	19.94	12.70		15.64	2x18	50.42	43.18		/
2x07	22.48	15.24		18.18	2x20	55.50	48.26		51.20
2x08	25.02	17.78		20.72	2x22	60.58	53.34		/
2x09	27.56	20.32		/	2x25	68.20	60.96		/
2x010	30.10	22.86		25.80	2x30	80.90	73.66		/
2x11	32.64	25.40		/	2x32	85.98	78.74		/
2x12	35.18	27.94		30.88	/				

X9555H3-2xXX-PTV01	PBT	Brass	X9555W-A
X9555H3-2xXXX-PTV01			
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X9555H3-2xXX-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X9555H3-2xXX-PTV01		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0

XKLE

XKB INDUSTRIAL PRECISION CO., LIMITED

广东星地科技股份有限公司

							ANGULAR	±5°
Δ _形		日期					≤ 4	±0.2
Δ _尺							4<L≤ 16	±0.3
Δ _数							16<L≤ 63	±0.4
MARK		DESCRIPTION		DATE	REVISED	APPROVED	L> 63	±0.5
文件工程章							UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn								