








Connector Chimerism(Reference)




PCB LAYOUT

Specifications:
规格:
Voltage rating:300V AC/DC
额定电压: 300V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1700V AC/minute
耐受电压: 1700V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X4001 W F - 02 - LP SN
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:Wafer
- 3.Category:F-Female
- 4.Row No.Pin No:02 Pin
- 5.Material:LP-LCP UL94V-0
- 6.Plating:SN-Tin Plated



X4001WF-02-LPSN	LCP	Phosphor Bronze	X4001WM
PART NO	Material	Material	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 4.0mm BTB Connector
DWN		VIEW:	PART NO.: X4001WF-02-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X4001WF-02-LPSN
APPD		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1/1
			A0

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5
UNSPECIFIED TOLERANCES	

XKLB

广东星坤科技股份有限公司

文件工程章	日期
MARK	DESCRIPTION
文件工程章	REVISIONS
文件工程章	DATE
文件工程章	REVISED
文件工程章	APPROVED
文件工程章	UNSPECIFIED TOLERANCES