




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ MAX
接触电阻: ≤20mΩ MAX

X9555 H I -2xXX A- PT AuN
① ②③ ④ ⑤⑥ ⑦

- 1. Series No
- 2. Category:H- HSG
- 3.Welding Board Angle:I-HSG+hardware
- 4.Row No-Pin No:2xXX-2x03P~2x32P
- 5.Special:NO:A-Resultant height 5.08mm
- 6.Material:PT-PBT UL94V-0
- 7.Plating:AuN-Terminal half- Gold nickel

NUMBER OF POSITIONS	DIMENSION		NUMBER OF POSITIONS	DIMENSION	
	A	B		A	B
2x03	12.98	5.08	2x12	35.84	27.94
2x04	15.52	7.62	2x13	38.38	30.48
2x05	18.06	10.16	2x15	43.46	35.56
2x06	20.6	12.70	2x17	48.54	40.64
2x07	23.14	15.24	2x20	56.16	48.26
2x08	25.68	17.78	2x22	61.24	53.34
2x09	28.22	20.32	2x25	68.86	60.96
2x10	30.76	22.86	2x30	81.56	73.66
2x11	33.3	25.40	2x32	86.64	78.74

X9555HI-2xXXA-PTAuN	PBT	Brass	XPDI.27-A28PXX-IDC	X9555H1-2xXX X9555H2-2xXX X9555H3-2xXX X9555H4-2xXX
PART NO	Material	Material(pn)	Suitable XKB flat cable	Suitable XKB IDC

DSND		SCALE: N/A	MODEL TYPE:		
DWN		VIEW:	2.54mm DIP		
CHKD		UNIT: mm/in	PART NO.: X9555HI-2xXXA-PTAuN		
APPD		SIZE: A4	DWG NO.: X-X9555HI-2xXXA-PTAuN		
			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED