






TYPE 1



Y型端子

14P-64P 双槽



6P 小鼻/无槽  
TYPE C

6P 大鼻/无槽  
TYPE A

8P 大鼻/无槽  
TYPE A

6P 小鼻/单槽  
TYPE B

8P 小鼻/单槽  
TYPE B

10P-12P 单槽  
Blank

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X9555 H2 -2xXX X- PT XX  
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:H2-three-piece with TYPE1 HSG
- 3.Row No-Pin No:2xXX-2x03P~2x32P
- 4.Special:NO:X Type A or Type B and Type C  
Blank-conventional product
- 5.Material:PT-PBT UL94V-0
- 6.Plating:V01-Gold Flash

|                     |          |               |             |                    |                         |                  |
|---------------------|----------|---------------|-------------|--------------------|-------------------------|------------------|
| X9555H2-2xXX-PTV01  | PBT      | BRASS         | Gold Flash  | X9555WV-2xXX       | XPD1.27-A28PXX-IDC      | X9555HI-2xXXA    |
|                     |          |               |             | X9555WR-2xXX       |                         | X9555HI-2xXXB    |
|                     |          |               |             | X9555WVS-2xXX      |                         | X9555HI-2xXXC    |
|                     |          |               |             | X9555WV-2xXX       |                         | X9555HI-2xXXA    |
|                     |          |               |             | X9555WR-2xXX       |                         | X9555HI-2xXXB    |
| X9555H2-2xXXX-PTV01 |          |               |             | X9555WVS-2xXX      |                         | X9555HI-2xXXC    |
| PART NO             | Material | Material(pin) | Finish(pin) | Suitable XK8 Water | Suitable XK8 flat cable | Suitable XK8 DIP |

| NUMBER OF POSITIONS | DIMENSION |       |           | NUMBER OF POSITIONS | DIMENSION |       |     |
|---------------------|-----------|-------|-----------|---------------------|-----------|-------|-----|
|                     | A         | B     | C         |                     | A         | B     | C   |
| 2x03                | 12.32     | 5.08  | 1.9       | 2x13                | 37.72     | 30.48 | 3.8 |
| 2x04                | 14.86     | 7.62  | 小1.9/大3.8 | 2x15                | 42.80     | 35.56 | 3.8 |
| 2x05                | 17.40     | 10.16 | 3.8       | 2x17                | 47.88     | 40.64 | 3.8 |
| 2x06                | 19.94     | 12.70 | 3.8       | 2x18                | 50.42     | 43.18 | 3.8 |
| 2x07                | 22.48     | 15.24 | 3.8       | 2x20                | 55.50     | 48.26 | 3.8 |
| 2x08                | 25.02     | 17.78 | 3.8       | 2x22                | 60.58     | 53.34 | 3.8 |
| 2x09                | 27.56     | 20.32 | 3.8       | 2x25                | 68.20     | 60.96 | 3.8 |
| 2x10                | 30.10     | 22.86 | 3.8       | 2x30                | 80.90     | 73.66 | 3.8 |
| 2x11                | 32.64     | 25.40 | 3.8       | 2x32                | 85.98     | 78.74 | 3.8 |
| 2x12                | 35.18     | 27.94 | 3.8       |                     |           |       |     |

|      |  |             |                                   |
|------|--|-------------|-----------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:                       |
| DWN  |  | VIEW:       | 2.54mm IDC                        |
| CHKD |  | UNIT: mm/in | PART NO.:<br>X9555H2-2xXXX-PTV01  |
| APPD |  | SIZE: A4    | DWG NO.:<br>X-X9555H2-2xXXX-PTV01 |



XXB INDUSTRIAL PRECISION CO.,LIMITED

| WEIGHT | SHEET | REVISION |
|--------|-------|----------|
|        | 1/1   | A0       |

|                                               |  |  |  |  | ANGLAR                 | ±5°  |
|-----------------------------------------------|--|--|--|--|------------------------|------|
| ΔX                                            |  |  |  |  | L≤ 4                   | ±0.2 |
| ΔX                                            |  |  |  |  | 4<L≤ 16                | ±0.3 |
| ΔX                                            |  |  |  |  | 16<L≤ 63               | ±0.4 |
| MARK                                          |  |  |  |  | L> 63                  | ±0.5 |
| REVISIONS                                     |  |  |  |  | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |                        |      |