



5.80[0.228]±0.20



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1500V AC/minute
 耐受电压: 1500V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧

X9555 H X-2xXX B-PTXX

① ②③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:H-HSG
- 3.Welding Board Angle:Blank-ordinary
- 4.Row No-Pin No:2xXX-2x02P~2x20P
- 5.Special No:B-Single gap
- 6.Material:PT-PBT 94V-0
- 7.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x02	2.54	9.54	2x12	27.94	34.94
2x03	5.08	12.08	2x13	30.48	37.48
2x04	7.62	14.62	2x14	33.02	40.02
2x05	10.16	17.16	2x15	35.56	42.56
2x06	12.70	19.70	2x16	38.10	45.10
2x07	15.24	22.24	2x17	40.64	47.64
2x08	17.78	24.78	2x18	43.18	50.18
2x09	20.32	27.32	2x19	45.72	52.72
2x10	22.86	29.86	2x20	48.26	55.26
2x11	25.40	32.40			

X9555H-2xXXB-PT	PBT UL 94V-0	X955T	X9555W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
ΔX	ΔX
ΔX	ΔX
MARK	文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	units: mm
				tolerance:
				X.X ±0.2mm
				X.XX ±0.1mm
				X.XXX ±0.05mm
				UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	Wire to board connector
CHKD	DATE	UNIT: mm/in	PART NO.: 2.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.: X9555H-2xXXB-PT
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0