


波峰焊温度: $255 \pm 5^{\circ}\text{C}$, 10S

X4611 F V - XX - C43 D28
 (1) (2) (3) (4) (5) (6)

- 1.Series No.
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180
- 4.Row No -Pin No:XX-02P-40P
- 5.Plastic height: C=4.3mm
- 6.Pin Length:D=2.8mm



X4611FV-XX-C43D28	PA6T	Brass	1U"Gold	X4611W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 2.00mm BTB Connector		
DWN		VIEW: 	PART NO.: X4611FV-XX-C43D28		
CHKD		UNIT: mm/in	DWG NO.: X-X4611FV-XX-C43D28		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISI A0

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司				ANGLAR	±5°
ΔX		日		L ≤ 4	±0.2
ΔX		期		4 < L ≤ 16	±0.3
ΔX				16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63 ±0.5
文件工程章				UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn					