



PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C ~ +105°C

温度范围: -40°C ~ +105°C

Insulation resistance: ≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U" Gold

镀层: 1U" Gold

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

X6511 F R - XX - C85 D32
① ② ③ ④ ⑤ ⑥

1. Series No.
2. Category: F-Female
3. Welding Board Angle: R-Stright 90°
4. Row No -Pin No: XX-02P-40P
5. Plastic height: C=8.5mm
6. Pin Length: D=3.2mm

X6511FR-XX-C85D32	PA6T	Brass	1U"Gold	X6511W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer

广东星坤科技股份有限公司	
DATE	日期
DESIGN	设计
MARK	文件工程章
DESCRIPTION	REVISIONS
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn	

					ANGULAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
					UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector		
DWN		VIEW: 	PART NO.: X6511FR-XX-C85D32		
CHKD		UNIT: mm/in	DWG NO.: X-X6511FR-XX-C85D32		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0