



SECTION A-A



SPECIFICATIONS 规范

Current rating 额定电流:3A AC,DC

Voltsge rating 额定电压:250VAC,DC

Temperaturerange 温度区间:-40℃~+105℃

Contact resistance 接触电阻:10mnMax

Insulation resistance 绝缘电阻:5000M2Min

Withstanding Voltage 耐压:750VAC/minute.

Material 原料:HSG:Nylon66 UL94V-2

TER:Brass.Tin plated

X9254 H IR - XX A - NO FX

① ② ③ ④ ⑤ ⑥ ⑦

①Series No.

②Category: H-HSG

③Welding Board Angle:

I-HSG+Hardware set products

Board-In:R-90°

④Row No.-Pin No.: XX-Single row

⑤Special No:

A- NO With Square corner

⑥Material: NO-PA66 94V-0

⑦Special No:

FA-Bevel one open.Red AWG#22

FB-Bevel one open.White AWG#24

FC-Bevel one open.Natural AWG#24

FD-Bevel one open.Black AWG#24

FE-Bevel one open.Blue AWG#26

FF-Bevel one open.Green AWG#26

C	Color	Wier size	C	Color	Wier size
A	Red	22AWG	D	Black	24AWG
B	White	24AWG	E	blue	26AWG
C	Natural	24AWG	F	Green	26AWG

NUMBER OF POSITIONS	DIMENSION A	NUMBER OF POSITIONS	DIMENSION A	NUMBER OF POSITIONS	DIMENSION A	NUMBER OF POSITIONS	DIMENSION A
02	5.08	09	22.86	16	40.64		
03	7.62	10	25.40	17	43.18		
04	10.16	11	27.94	18	45.72		
05	12.70	12	30.48	19	48.26		
06	15.24	13	33.02	20	50.80		
07	17.78	14	35.56				
08	20.32	15	38.10				

						DSND		SCALE: N/A	MODEL TYPE: 2.54mm IDC Style Connectors
ΔX					ANGLAR	±5°		VIEW:	PART NO.: X9254HIR-XXA-NOFX
ΔX					L ≤ 4	±0.2		UNIT: mm/in	DWG NO.: X-X9254HIR-XXA-NOFX
ΔX					4 < L ≤ 16	±0.3		SIZE: A4	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4			
					L > 63	±0.5			
REVISIONS						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn							WEIGHT	SHEET	REVISION
								1/1	A0