

Specification Sheet

Part Number: 155-01600



Clip can be installed by hand – no need for hardware or tools.
Design provides low insertion and high extraction force, for simple, secure performance.
Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.57" Long, 0.26 - 0.28" Mounting Hole, PA66HIRHS, Black 500/pkg

Article Number	155-01600
Type	STAND-OFF-CLIP-2
Color	Black (BK)
Quantity Per	bag
Product Description	Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.
Short Description	Standoff Bundling Clip, 1.57" Long, 0.26 - 0.28" Mounting Hole, PA66HIRHS, Black 500/pkg

Global Part Name	STAND-OFF-CLIP-2-PA66HIRHS-BK
------------------	-------------------------------

Length L (Imperial)	1.57
---------------------	------

Length L (Metric)	40.0
-------------------	------

Offset Length (Imperial)	0.98
--------------------------	------

Offset Length (Metric)	25.0
------------------------	------

Fixation Method	Arrowhead
-----------------	-----------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.06
--------------------------------	------

Panel Thickness Min (Metric)	0.4
------------------------------	-----

Panel Thickness Max (Metric)	1.6
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26 - 0.27
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	6.5 - 6.8 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.26
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.8
---------------------------------------	-----

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).