

## Specification Sheet

Part Number: 156-02288



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 5 mm, 16 mm, PA66HIRHSUV, Black, 2000/ctn

|                     |                                                                                                                                                                    |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 156-02288                                                                                                                                                          |
| Type                | MOC5FMOC16M                                                                                                                                                        |
| Color               | Black (BK)                                                                                                                                                         |
| Quantity Per        | carton                                                                                                                                                             |
| Product Description | The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other. |
| Short Description   | MOC Clip to MOC Clip, 5 mm, 16 mm, PA66HIRHSUV, Black, 2000/ctn                                                                                                    |
| Global Part Name    | MOC5FMOC16M-PA66HIRHSUV-BK                                                                                                                                         |

|                                |                                                                          |
|--------------------------------|--------------------------------------------------------------------------|
| Length L (Imperial)            | 1.48                                                                     |
| Length L (Metric)              | 37.7                                                                     |
| Variant                        | Clip to Clip                                                             |
| Bundle Diameter Min (Imperial) | 0.16                                                                     |
| Bundle Diameter Min (Metric)   | 4.0                                                                      |
| Bundle Diameter Max (Imperial) | 0.22                                                                     |
| Bundle Diameter Max (Metric)   | 5.5                                                                      |
| Height H (Imperial)            | 1.01                                                                     |
| Height H (Metric)              | 25.7                                                                     |
| Depth D (Imperial)             | 0.47                                                                     |
| Depth D (Metric)               | 12.0                                                                     |
| Material                       | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut              | PA66HIRHSUV                                                              |
| Flammability                   | UL 94 HB                                                                 |
| Halogen Free                   | Yes                                                                      |

|                              |                                   |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No)        | Yes                               |
| Operating Temperature        | -40°F to +230°F (-40°C to +110°C) |
| Reach Compliant (Article 33) | No                                |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 2000                              |
| Package Quantity (Metric)    | 2000                              |
| Customs Number               | 3926909988                        |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)