







XKB



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X9357 W R -2xXX - XX XX
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:W-wafer
- 3.Welding Board Angle:R-90
- 4.Row No.-Pin No: 2xXXPin
- 5.Material: N0-PA66 94V-0; N2-PA66 94V-7
LP-LCP 94V-0; 6T-PA6T 94V-0; 9T-PA9T94V-0
- 6.Planting Category: V01:All Gold-Plated Gold Flash;
SN-Bright Tin plating 70u"

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	5.60	—	2x07	30.80	25.20
2x02	9.80	4.20	2x08	35.00	29.40
2x03	14.00	8.40	2x09	39.20	33.60
2x04	18.20	12.60	2x10	43.40	37.80
2x05	22.40	16.80	2x11	47.60	42.00
2x06	26.60	21.00	2x12	51.80	46.20

X9357WR-2xXX-N0V01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X9357H	1,000Pcs
X9357WR-2xXX-N0SN	Nylon66 UL94V-0	Brass	Tin-Plated		
X9357WR-2xXX-N2V01	Nylon66 UL 94V-2	Brass	Gold-Flash		
X9357WR-2xXX-N2SN	Nylon66 UL 94V-2	Brass	Tin-Plated		
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB	Q'ty/Bag

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

				ANGLAR	±5°
				L≤ 4	±0.2
				4<L≤ 16	±0.3
				16<L≤ 63	±0.4
PTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS				UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

DSND		SCALE: N/A	MODEL TYPE: 4.2 mm Crimp Style Connecto			
DWN		VIEW:	PART NO.: X9357WR-2xXX-XXXX			
CHKD		UNIT: mm/in	DWG NO.: X-X9357WR-2xXX-XXXX			
APPD		SIZE: A4				
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISIC A0	