

备注(NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680), 镍底, 镀金0.5U

1.3 外壳: 不锈钢304—表面镀镍50U

2. 电气特性:

2.1 接触区: 接触电阻30mQMax,
允许10mΩ变化量,

测试条件: 20mv, 100mA下测量,

2.2 接触电流: 3AVBUS引脚: 1.25A

用于GND引脚; 其他引脚为0.25A.

2.3 额定电压: 5V.

2.4 耐电压: 100VAC.

2.5 绝缘电阻: 至少100兆欧

3. 机械性能:








3.1 插入力: 0.5—2.0Kg

3.2 拔出力: 0.6—2.0Kg


3.3 插拔次数: 5000+.

4. 工作环境: -20℃to +85℃

4.1 盐雾测试: 24H



SECTION A-A



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE: USB-type c 6pin每座立贴
L=5.5mm成品

PAR TYPE-C-336-LSRH550

DECIMALS:

ANGLES:

.X:±0.35

.X':±2°

.XX:±0.25

.XX':±1°

.XXX:±0.15

CUSTOMER COPY

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:1F1 REV:A