


接触电阻: 20mΩ max

①      ②   ③   ④   ⑤

1. Series No  
2. Category: H-Housing  
3. Housing Type: M-Male Housing  
4. Row No. Pin No: XX-01~03P  
5. Material: N0-PA66 94V-0

| Poles | Dimensions(mm) |       |
|-------|----------------|-------|
|       | A              | B     |
| 02    | 8.28           | 11.00 |
| 03    | 12.42          | 15.14 |



2P~3P

|               |          |                       |                         |                          |
|---------------|----------|-----------------------|-------------------------|--------------------------|
| X4140HM-XX-N0 | PA66     | X4140W                | X4140HF                 | X4140TF                  |
| PART NO       | Material | Suitable XKB<br>Wafer | Suitable XKB<br>Housing | Suitable XKB<br>Terminal |

|                        |  |                                                                                             |                                             |              |                |
|------------------------|--|---------------------------------------------------------------------------------------------|---------------------------------------------|--------------|----------------|
| DSND                   |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>4.14mm Crimp Style Connector |              |                |
| DWN                    |  | VIEW:  | PART NO.:<br>X4140HM-XX-N0                  |              |                |
| CHKD                   |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X4140HM-XX-N0                 |              |                |
| APPD                   |  | SIZE: A4                                                                                    |                                             |              |                |
| PRECISION CO., LIMITED |  |                                                                                             | WEIGHT                                      | SHEET<br>1/1 | REVISION<br>A0 |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                            |             |      |         |          | L ≤ 4                  | ±0.2 |
| ΔX                                            |             |      |         |          | 4 < L ≤ 16             | ±0.3 |
| ΔX                                            |             |      |         |          | 16 < L ≤ 63            | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L > 63                 | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |