



Recommended PCB Layout(Top view)
Tolerance:±0.05mm

Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 1000V AC/分钟
Temperature range:-25℃~+105℃
温度范围: -25℃~+105℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ

X2016 W V - XX R - LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~16Pin
- 5.Special No:R-DIP 2.2mm
- 6.Material:LP-LCP UL94V-0 ,Natural
- 7.Plating:SN- Tin Plated

| Poles | Dimensions (mm) | | | Poles | Dimensions (mm) | | |
|-------|-----------------|-------|-------|-------|-----------------|-------|-------|
| | A | B | C | | A | B | C |
| 02 | 2.00 | 4.90 | 6.00 | 10 | 18.00 | 20.90 | 22.00 |
| 03 | 4.00 | 6.90 | 8.00 | 11 | 20.00 | 22.90 | 24.00 |
| 04 | 6.00 | 8.90 | 10.00 | 12 | 22.00 | 24.90 | 26.00 |
| 05 | 8.00 | 10.90 | 12.00 | 13 | 24.00 | 26.90 | 28.00 |
| 06 | 10.00 | 12.90 | 14.00 | 14 | 26.00 | 28.90 | 30.00 |
| 07 | 12.00 | 14.90 | 16.00 | 15 | 28.00 | 30.90 | 32.00 |
| 08 | 14.00 | 16.90 | 18.00 | 16 | 30.00 | 32.90 | 34.00 |
| 09 | 16.00 | 18.90 | 20.00 | | | | |

| X2016WV-XXR-LPSN | LCP | Brass | X2016H |
|------------------|----------|---------------|----------------------|
| PART NO | Material | Material(Pin) | Suitable XKB Housing |

| | | | |
|------|--|-------------|--|
| DSND | | SCALE: N/A | MODEL TYPE: 2.0mm Crimp Style Connector |
| DWN | | VIEW: | PART NO.: X2016WV-XXR-LPSN |
| CHKD | | UNIT: mm/in | DWG NO.: X-X2016WV-XXR-LPSN |
| APPD | | SIZE: A4 | WEIGHT SHEET REVISION |
| | | | 1/1 A0 |



XKB INDUSTRIAL PRECISION CO.,LIMITED

| | |
|------------------------|------|
| ANGLAR | ±5° |
| L ≤ 4 | ±0.2 |
| 4 < L ≤ 16 | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63 | ±0.5 |
| UNSPECIFIED TOLERANCES | |

广东星坤科技股份有限公司

| | |
|------|-------------|
| 件 | 日期 |
| 效 | |
| MARK | DESCRIPTION |
| 文件 | 工程章 |

| REVISIONS | DATE | REVISED | APPROVED |
|-----------|------|---------|----------|
| | | | |

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn