



PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C~+105°C

温度范围: -40°C~+105°C

Insulation resistance: ≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U"Gold

镀层: 1U"Gold

Reflow soldering temperature: 260±5°C, 10S

回流焊温度: 260±5°C, 10S

X4611 F R S - XX - C43 D42
① ② ③ ④ ⑤ ⑥ ⑦

1. Series No

2. Category: F-Female

3. Welding Board Angle: R-Stright 90°

4. Welding Way: S-SMT

5. Row No. Pin No: XX-01~40 Pin

6. Plastic height: C=4.3mm

7. Pin Length: D=4.2mm

X4611FRS-XX-C43D42	PA6T	Brass	X4611W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

广东星坤科技股份有限公司	
Δ年	日期
Δ月	
Δ日	
Δ数	
MARK	文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
REVISIONS				
ANGLAR	±5°			
L ≤ 4	±0.2			
4 < L ≤ 16	±0.3			
16 < L ≤ 63	±0.4			
L > 63	±0.5			

XKB

DSND		SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector		
DWN		VIEW: 	PART NO.: X4611FRS-XX-C43D42		
CHKD		UNIT: mm/in	DWG NO.: X-X4611FRS-XX-C43D42		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED