






Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: 40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

X3025 W V - 2xXX - LP V01
① ② ③ ④ ⑤ ⑥

1.Series No



2.Category:W-Wafer

3.Welding Board Angle:V-Straight 180°

4.Row No.Pin No:2xXX-2x01~2x12P

6.Material:LP-LCP 94V-0

6.Plating:SW-Matte Tin V01:Gold 1u"



PCB LAYOUT

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	/	6.65	2x07	18.00	24.65
2x02	3.00	9.65	2x08	21.00	27.65
2x03	6.00	12.65	2x09	24.00	30.65
2x04	9.00	15.65	2x10	27.00	33.65
2x05	12.00	18.65	2x11	30.00	36.65
2x06	15.00	21.65	2x12	33.00	39.65

X3025WV-2xXX-LPSW	LCP	Brass	Matte Tin	X3025HM
X3025WV-2xXX-LPV01			Gold 1u"	
PART NO	Material	Material(Pin)	Finish	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X3025WV-2xXX-LPV01
CHKD		UNIT: mm/in	DWG NO.: X-X3025WV-2xXX-LPV01
APPD		SIZE: A4	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
					L> 63	±0.5

UNSPECIFIED TOLERANCES

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED