

备注(NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680), 镍底, 镀金0.5U

1.3 外壳: 不锈钢304—表面镀镍50U

2. 电气特性:

2.1. 接触区: 接触电阻 30mQMax,

允许 10mΩ 变化量,

测试条件: 20mv, 100mA 下测量,

2.2. 接触电流: 3AVBUS 引脚: 1.25A

用于 GND 引脚: 其他引脚为 0.25A.

2.3. 额定电压: 5V.

2.4. 耐电压: 100VAC.

2.5. 绝缘电阻: 至少 100 兆欧

3. 机械性能:




3.1. 插入力: 0.5—2.0Kg

3.2. 拔出力: 0.6—2.0Kg

3.3. 插拔次数: 5000+.

4. 工作环境: -20℃to +85℃

4.1. 盐雾测试: 24H



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE: USB—type C 6pin 母座 LSR
L=6.0mm 成品

PAR TYPE—C—336—LSRH600

DECIMALS:

ANGLES:

.X: ±0.35

.X': ±2°

.XX: ±0.25

.XX': ±1°

.XXX: ±0.15

CUSTOMER COPY

SCALE: 1:1 UNIT: MM

SIZE: A4 SHEET: 1F1



REV: A