








RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

备注(NOTE):1材质:

- 1.1胶芯:LCP UL94 V-0
- 1.2端子:(C2680,;镍底,镀金0.5U
- 1.3外壳:不锈钢201—表面镀镍50U
- 2.电气特性:
 - 2.1.接触区:接触电阻30mQMax, 允许10mΩ变化量, 测试条件:20mv,100mA T测量,
 - 2.2.额定电流:最大3A
 - 2.3.额定电压:5V.
 - 2.4.耐受电压:100VAC.
 - 2.5.绝缘电阻:至少100兆欧
- 3.机械性能:
 - 3.1.插入力:0.5—2.0Kg
 - 3.2.拔出力:0.8—2.0Kg
 - 3.3.插拔次数:5000+.
- 4.工作环境: -20℃to +85℃
- 4.1.盐雾测试:24H

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:USB-type C 6pin 母座
沉板0.8MM—成品

PAR TYPE-C-335-WFRSC08L68

DECIMALS:

ANGLES:

.X:±0.35

.X':±2°

.XX:±0.25

.XX':±1°

.XXX:±0.15

CUSTOMER COPY

SCALE1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A