



300V 7A 24-18AWG 1.0mm²

Poles: 2P, 3P-24P

Pitch: 3.81mm(.150")

Materials

Housing: PA66(UL 94V-0)

Spring: Phosphor Bronze

Solder Pin: Brass, Tin Plated

Screw: M2, Steel (A3), Zinc Plated

Torque: 0.2N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
新莱亚电子 XINLAIYA ELECTRONIC CO., LTD		图名/Title XY340V	文件编号/File No.		±.1		±.1
					±.2	±.2	
					±.3	±.3	
					±.4	±.4	
			页序/Sheet		±.5		±.5
备注/Remark				单位/Unit: mm			