






序号 /RevNo.	名称 /Title	文件编号 /File No.
1	XY128A 塑件	QJ/XYT-2140101
2	XY128 铜方块	QJ/XYT-2140102
3	XY128V-A 端子	QJ/XYT-2140103
4	XY103 螺丝	QJ/XYT-2140104

300V 15A 24-12AWG 2.5mm²

Poles: 2P&3P-24P

Pitch: 5.08mm

Materials

Housing: PA66(UL 94V-0)

Wire Cage: Brass,Nickel Plated

Solder Pin: Brass,Tin Plated

Screw: M2.5,Steel(A3),Zinc Plated

Torque: 0.4N.m

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance			
新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD		图名 /Title	文件编号 /File No.		x, ± 0.2	x", ± 2"	
		XY128VA-5.08 产 品 图	QJ/XYT-2240200		.x ± 0.1	.x' ± 1"	
			页 序 /Sheet		.xx ± 0.05	.xx' ± 0.5"	
					.xxx ± 0.01		
		备注 /Remark				单位 /Units: mm	

序号 /RevNo.	更改记录 /Revision note	签名 /Signature	日期 /Date
------------	---------------------	---------------	----------