











适用扁平线(Applicable Flat Cable)



SECTION A-A



序号	品名	材质
①	1.0K型胶芯(H2.5) 1.0K Type Housing(H2.5)	LCP UL94V-0 本色 Natural
②	1.0K型下端子(H2.5) 1.0K Type Under Terminal(H2.5)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	1.0K型卧式后盖(H2.5) 1.0K Type Actuator(H2.5)	LCP UL94V-0 黑色 Black
④	1.0K型卧式焊片(H2.5) 1.0K Type Fitting Nail(H2.5)	黄铜/表面镀锡 Brass/Tin Plating

CKT	A	B	C
4	3.00	5.06	11.10
5	4.00	6.06	12.10
6	5.00	7.06	13.10
7	6.00	8.06	14.10
8	7.00	9.06	15.10
9	8.00	10.06	16.10
10	9.00	11.06	17.10
11	10.00	12.06	18.10
12	11.00	13.06	19.10
13	12.00	14.06	20.10
14	13.00	15.06	21.10
15	14.00	16.06	22.10
16	15.00	17.06	23.10
18	17.00	19.06	25.10
19	18.00	20.06	26.10
20	19.00	21.06	27.10
22	21.00	23.06	29.10
24	23.00	25.06	31.10
25	24.00	26.06	32.10
26	25.00	27.06	33.10
28	27.00	29.06	35.10
30	29.00	31.06	37.10
32	31.00	33.06	39.10
35	34.00	36.06	42.10
36	35.00	37.06	43.10
40	39.00	41.06	47.10

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALE: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	10B25LXXP	UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	10B25LXXP	SPECIFIED,TOLERANCE:		X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	