


适用扁平线(Applicable Flat Cable)



适用线路板(PCB LAYOUT)

序号 (NO.)	品名 (Name)	材质 (Material)
①	0.5后锁胶芯(H=2.0) 0.5 PH BackFlip Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	0.5后锁端子(H=2.0) 0.5 PH BackFlip Type Terminal (H=2.0)	磷青铜/表面镀金 Phosphor Bronze/ Gold Plating
③	0.5后锁后盖(H=2.0) 0.5 PH BackFlip Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	0.5后锁焊片(H=2.0) 0.5 PH BackFlip Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CKT	A	B	C	CKT	A	B	C
4	1.5	2.56	5.5	33	16.0	17.06	20.0
5	2.0	3.06	6.0	34	16.5	17.56	20.5
6	2.5	3.56	6.5	35	17.0	18.06	21.0
7	3.0	4.06	7.0	36	17.5	18.56	21.5
8	3.5	4.56	7.5	37	18.0	19.06	22.0
9	4.0	5.06	8.0	38	18.5	19.56	22.5
10	4.5	5.56	8.5	39	19.0	20.06	23.0
11	5.0	6.06	9.0	40	19.5	20.56	23.5
12	5.5	6.56	9.5	41	20.0	21.06	24.0
13	6.0	7.06	10.0	42	20.5	21.56	24.5
14	6.5	7.56	10.5	43	21.0	22.06	25.0
15	7.0	8.06	11.0	44	21.5	22.56	25.5
16	7.5	8.56	11.5	45	22.0	23.06	26.0
17	8.0	9.06	12.0	46	22.5	23.56	26.5
18	8.5	9.56	12.5	47	23.0	24.06	27.0
19	9.0	10.06	13.0	48	23.5	24.56	27.5
20	9.5	10.56	13.5	49	24.0	25.06	28.0
21	10.0	11.06	14.0	50	24.5	25.56	28.5
22	10.5	11.56	14.5	51	25.0	26.06	29.0
23	11.0	12.06	15.0	52	25.5	26.56	29.5
24	11.5	12.56	15.5	53	26.0	27.06	30.0
25	12.0	13.06	16.0	54	26.5	27.56	30.5
26	12.5	13.56	16.5	55	27.0	28.06	31.0
27	13.0	14.06	17.0	56	27.5	28.56	31.5
28	13.5	14.56	17.5	57	28.0	29.06	32.0
29	14.0	15.06	18.0	58	28.5	29.56	32.5
30	14.5	15.56	18.5	59	29.0	30.06	33.0
31	15.0	16.06	19.0	60	29.5	30.56	33.5
32	15.5	16.56	19.5	80	39.5	40.56	43.5

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	05A20HXXG	UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	05A20HXXG	SPECIFIED,TOLERANCE:	X.x ±0.20			
						X.xx ±0.15			
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	