



技术参数

1. 额定电流:50mA 12V DC
2. 接触电阻:100毫欧
3. 行程:0.15±0.05mm
4. 绝缘电阻:100兆欧
5. 抗电强度:100v 50Hz 1Min



电器原理图



P C B 参考图

PAPT NO	TS2030E-X-X
Operating Force	160 : 160gf ; 260 : 260gf
Height	58 : 0.58mm

E	按键点	聚锌亚胺	new		2015/5/3	A	瀚源	
D	防尘膜	PI膜	ECN BO.		DATE.	REV.		
C	簧片	不锈钢覆银	DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALE: 1/2	
B	基座	LCP	Mikey	Tom	Jerry	PART NAME	TS2030E-X-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°
A	卡件	磷铜0.08				MODEL NAME	TS2030E-X-X	
序号	名称	材料				3RD ANGLE PROJ	HanElectricity Co.,LTD	