




电路图



PCB线路板安装图(±0.1)

项目	规格
额定负荷	DC 12V 50mA
绝缘电阻	100MΩ min. 100v Dc
耐压强度	AC250V 50HZ 1min
电器寿命	≤10000次
环境温度	-25~70℃
相对湿度	(40℃) ≤95%
接触电阻	50mΩ max
行程	0.20±0.05mm
动作力	260gf±20gf

PAPT NO	TC1109DE-X-X	
Operating Force	160 : 160gf ; 260 : 260gf	
Height	38 : 3.8mm	65 : 6.5mm
	43 : 4.3mm	70 : 7.0mm
	45 : 4.5mm	75 : 7.5mm
	50 : 5.0mm	80 : 8.0mm
	55 : 5.5mm	85 : 8.5mm
	60 : 6.0mm	90 : 9.0mm

DESIGNED		CHECKED		APPROVAL		DRAWING NUMBER		DATE		REV.		SCALE	
Mikey		Tom		Jerry		PART NAME		TC1109DE-X-X		UNLESS OTHERWISE SPECIFIED, TOLERANCE:		X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3	
ECN BO.		DESCRIPTION.		DATE.		REV.		SCALE: 1/2		SCALE: 3:1		FILE.NO.	
new		2015/5/3		A		HanElectricity Co.,LTD							

瀚源